# HellermannTyton

#### IMP3.510C2

Article Number: 151-42359

IMP Plate, 3.5" X .75", Nylon, White, 100/pkg



RoHS

#### **Base Data**

Local Order Number IMP3.510C2

Type IMP3.5

Color White (WH)

Features and Benefits • Identification Marker Plates can be marked with a permanent pen, printed labels or hot stamped for a wide variety of

· Any size bundle diameter can be marked because it is only dependent upon the length of the cable tie selected,

provided the cable tie width does not exceed .29".

• The marker plates are stamped from nylon, making them a durable and long term method of identification. The mounting holes allow the marker to be mounted as a flag, tag or wrapped around the cable or bundle for a wide

variety of installed positions.

**Product Description** Identification Marker Plates can be mounted in any direction, either vertically or horizontally as flags, tags or

wraparound identification plates. They can be marked with HellermannTyton marking pens (T82-R or T82-S), thermal

transfer or laser labels or hot stamped. The markers are manufactured from nylon and are white in color.

Identification Plate Position attached to bundle

Mounting method Identification ETIM Others

Recommended Labels TAG75T1-822

Variant Other

Short Description IMP Plate, 3.5" X.75", Nylon, White, 100/pkg

With label space ETIM Yes

### **Product Dimensions**

Length L (imperial) 3.5 "

Length L (metric) 88.9 mm

Length L2 (imperial) 3.02 "

Length L2 (metric) 76.9 mm

Width W (imperial) 0.75 "

Width W (metric) 19.05 mm

Cable Tie Width Max (imperial) 0.18 "

Cable Tie Width max. (metric) 4.80 mm

Thickness T (imperial) 0.016 "

Thickness T (Metric) 0.4

#### **Logistics and Packaging**

Quantity per bag

Package Quantity (imperial) 100

Package Quantity 100

Carton Quantity 100 Pieces

## **Material and Specifications**

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL94 V2

Halogenfree Yes

Operating Temperature  $-40 \, ^{\circ}\text{F}$  to +185  $^{\circ}\text{F}$  (-40  $^{\circ}\text{C}$  to +85  $^{\circ}\text{C}$ )

ROHS Conformity Yes